


VFS4000 Series Manifold Specifications



Plug-in Type: With Terminal Block

- Since lead wires of solenoid valve are connected with the terminals on upper surface of terminal block, corresponding lead wires from power source can be wired at the bottom of terminal block.



VV5FS4-01T-06 1-03

VFS4000 Series Manifold
Plug-in type with terminal block

Stations

02	2 stations
:	:
10	10 stations

CE-compliant

Nil	—
Q	CE-compliant

Port size

Symbol	P, R1, R2	A, B
03		3/8
04	1/2	1/2
M		Mixed

Thread type

Nil	Rc
N*	NPT
T*	NPTF
F*	G


Symbol

Symbol	Passage		Porting specifications (A, B)
	P	R1, R2	
1	Common	Common	Side
2	Common	Common	Bottom*

* For bottom ported, 3/8 is only available.
* Semi-standard

Plug-in Type: With Multi-connector (Wiring specifications: Refer to page 1013.)

- Master connection of power and solenoid valves.
- Quick wiring permits easier installation.



VV5FS4-01C D-05 2-03

VFS4000 Series Manifold
Plug-in type with multi-connector

Stations

02	2 stations
:	:
08*	8 stations

* Max. 8 stations

CE-compliant

Nil	—
Q	CE-compliant

Port size

Symbol	P, R1, R2	A, B
03		3/8
04	1/2	1/2
M		Mixed

Thread type

Nil	Rc
N*	NPT
T*	NPTF
F*	G

Connector mounting direction

D	D side mounting
U	U side mounting


Symbol

Symbol	Passage		Porting specifications (A, B)
	P	R1, R2	
1	Common	Common	Side
2	Common	Common	Bottom*

* For bottom ported, 3/8 is only available.
* Semi-standard

Plug-in Type With: D-sub Connector (Wiring specifications: Refer to page 1013.)

- Wide range of interchangeability (MIL Spec D-sub connector terminal 25 pcs attached.)
- Quick wiring permits easier installation.



VV5FS4-01F D-06 1-03

VFS4000 Series Manifold
Plug-in type with D-sub connector

Stations

02	2 stations
:	:
08*	8 stations

* Max. 8 stations

CE-compliant

Nil	—
Q	CE-compliant

Port size

Symbol	P, R1, R2	A, B
03		3/8
04	1/2	1/2
M		Mixed

Thread type

Nil	Rc
N*	NPT
T*	NPTF
F*	G

Connector mounting direction

D	D side mounting
U	U side mounting


Symbol

Symbol	Passage		Porting specifications (A, B)
	P	R1, R2	
1	Common	Common	Side
2	Common	Common	Bottom*

* For bottom ported, 3/8 is only available.
* Semi-standard

Non Plug-in Type: Grommet Terminal, DIN Terminal

- Wiring for every valve.



VV5FS4-10-05 2-03

VFS4000 Series Manifold
Non plug-in type

Stations

02	2 stations
:	:
10	10 stations

CE-compliant

Nil	—
Q	CE-compliant

Port size

Symbol	P, R1, R2	A, B
03		3/8
04	1/2	1/2
M		Mixed

Thread type

Nil	Rc
N*	NPT
T*	NPTF
F*	G

Symbol

Symbol	Passage		Porting specifications (A, B)
	P	R1, R2	
1	Common	Common	Side
2	Common	Common	Bottom*

* For bottom ported, 3/8 is only available.
* Semi-standard