

Nozzles for Blowing

KN Series




Nozzle with self-align fitting/KN

(mm)



Model	Nozzle size øD	Applicable tubing O.D.	Width across flats		L ₁	M	Weight (g)
			H ₁	H ₂			
KN-04-100	ø1	ø4	10	10	27	15	13
KN-04-150	ø1.5	ø4	10	10	27.7	15	14
KN-06-100	ø1	ø6	12	12	30.1	16	19
KN-06-150	ø1.5	ø6	12	12	30.8	16	20
KN-06-200	ø2	ø6	12	12	31.5	16	22
KN-08-150	ø1.5	ø8	14	14	33.8	16	28
KN-08-200	ø2	ø8	14	14	34.6	16	30
KN-10-250	ø2.5	ø10	14	17	35.6	17	35
KN-10-300	ø3	ø10	14	17	36.3	17	36
KN-10-350	ø3.5	ø10	14	17	37.1	17	37
KN-10-400	ø4	ø10	14	17	29.5	17	30
KN-10-600	ø6	ø10	14	17	27.7	17	28
KN-12-350	ø3.5	ø12	17	19	40.4	17	54
KN-12-400	ø4	ø12	17	19	41.3	17	55
KN-12-600	ø6	ø12	17	19	31.2	17	40
KN-16-400	ø4	ø16	22	24	40.1	17	77
KN-16-600	ø6	ø16	22	24	38.4	17	79
KN-20-400	ø4	ø20	26	27	45.6	17	117
KN-20-600	ø6	ø20	26	27	43.9	17	112




Nozzle with male thread/KN

(mm)



Model	Nozzle size øD	Connection thread	Width across flats		L ₁	A*	Weight (g)
			H ₁	H ₂			
KN-R01-100	ø1	R 1/8	10	21.4	17.4	8	
KN-R01-150	ø1.5	R 1/8	10	21	17	8	
KN-R02-100	ø1	R 1/4	14	31.4	25.4	19	
KN-R02-150	ø1.5	R 1/4	14	31	25	20	
KN-R02-200	ø2	R 1/4	14	30.5	24.5	21	
KN-R02-250	ø2.5	R 1/4	14	30.1	24.1	21	
KN-R02-600	ø6	R 1/4	14	27.1	21.1	22	
KN-R03-400	ø4	R 3/8	17	31.8	25.4	36	
KN-R03-600	ø6	R 3/8	17	30.1	23.7	37	
KN-R04-400	ø4	R 1/2	22	41.8	33.6	75	
KN-R04-600	ø6	R 1/2	22	40.1	31.8	76	
KN-R06-600	ø6	R 3/4	27	49.6	40.1	149	
KN-R06-800	ø8	R 3/4	27	47.8	38	152	
KN-R10-800	ø8	R 1	36	62.8	52.4	328	

* Reference dimensions after R thread installation.




Copper extension nozzle/KNL

(mm)



Model	Nozzle size øD	Outside diameter	L ₁	Weight (g)
KNL3-06-150	ø1.5	ø6	300	43
KNL3-06-200	ø2	ø6	300	43
KNL3-08-200	ø2	ø8	300	61
KNL3-08-250	ø2.5	ø8	300	61
KNL3-10-250	ø2.5	ø10	300	94
KNL3-10-300	ø3	ø10	300	94
KNL6-06-150	ø1.5	ø6	600	84
KNL6-06-200	ø2	ø6	600	84
KNL6-08-200	ø2	ø8	600	117
KNL6-08-250	ø2.5	ø8	600	117
KNL6-10-250	ø2.5	ø10	600	183
KNL6-10-300	ø3	ø10	600	183



VMG

KN