

品名 품 명 Model	外径 외경(mm) Outer Dia.	内径 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	密着長 밀착장(mm) Solid Length	定数 정수(kgf/mm) spring constant	30万 (0.3million)		50万 (0.5million)		100万 (1million)	
						変形量 변형량(mm) Deflection	荷重 하중(kgf) Load	変形量 변형량(mm) Deflection	荷重 하중(kgf) Load	変形量 변형량(mm) Deflection	荷重 하중(kgf) Load
SU 10.5×15	10.5	6	15	4.5	0.78	9	7	8.3	6.4	7.5	5.8
20			20	6.0	0.58	12		11.0		10.0	
25			25	7.5	0.47	15		13.8		12.5	
30			30	9.0	0.39	18		16.5		15.0	
35			35	10.5	0.33	21		19.3		17.5	
40			40	12.0	0.29	24		22.0		20.0	
45			45	13.5	0.26	27		24.8		22.5	
50			50	15.0	0.23	30		27.5		25.0	
55			55	16.5	0.21	33		30.3		27.5	
60			60	18.0	0.19	36		33.0		30.0	
65			65	19.5	0.18	39		35.8		32.5	
70			70	21.0	0.17	42		38.5		35.0	
75			75	22.5	0.16	45		41.3		37.5	
80			80	24.0	0.15	48		44.0		40.0	
SU 12.5×15	12.5	7	15	4.5	0.89	9	8	8.3	7.4	7.5	6.7
20			20	6.0	0.67	12		11.0		10.0	
25			25	7.5	0.53	15		13.8		12.5	
30			30	9.0	0.44	18		16.5		15.0	
35			35	10.5	0.38	21		19.3		17.5	
40			40	12.0	0.33	24		22.0		20.0	
45			45	13.5	0.30	27		24.8		22.5	
50			50	15.0	0.27	30		27.5		25.0	
55			55	16.5	0.24	33		30.3		27.5	
60			60	18.0	0.22	36		33.0		30.0	
65			65	19.5	0.20	39		35.8		32.5	
70			70	21.0	0.19	42		38.5		35.0	
75			75	22.5	0.18	45		41.3		37.5	
80			80	24.0	0.17	48		44.0		40.0	
90	90	27.0	0.15	54	49.5	45.0					
100	100	30.0	0.13	60	55.0	50.0					
SU 14.5×15	14.5	8.5	15	4.5	1.11	9	10	8.3	9.2	7.5	8.3
20			20	6.0	0.83	12		11.0		10.0	
25			25	7.5	0.67	15		13.8		12.5	
30			30	9.0	0.56	18		16.5		15.0	
35			35	10.5	0.48	21		19.3		17.5	
40			40	12.0	0.42	24		22.0		20.0	
45			45	13.5	0.37	27		24.8		22.5	
50			50	15.0	0.33	30		27.5		25.0	
55			55	16.5	0.30	33		30.3		27.5	
60			60	18.0	0.28	36		33.0		30.0	
65			65	19.5	0.26	39		35.8		32.5	
70			70	21.0	0.24	42		38.5		35.0	
75			75	22.5	0.22	45		41.3		37.5	
80			80	24.0	0.21	48		44.0		40.0	
90			90	27.0	0.19	54		49.5		45.0	
100			100	30.0	0.17	60		55.0		50.0	
110	110	33.0	0.15	66	60.5	55.0					
120	120	36.0	0.14	72	66.0	60.0					
125	125	37.5	0.13	75	68.8	62.5					
150	150	45.0	0.11	90	82.5	75.0					