

SB-C-SA

■ SUPER CARBIDE BUR

Shank dia. $\phi 6\text{mm}$
Aluminum Cut

★ marked items : all carbide



Item No. (S. cut)	Size(mm)		
	L	L1	D
SB1C01SA★	50	19	6
SB1C02SA	63	19	9.5
SB1C03SA	69	25	12.7
SB1C04SA	69	25	16
SB1C05SA	69	25	19

Item No. (S. cut)	Size(mm)		
	L	L1	D
SB2C01SA★	50	19	6
SB2C02SA	63	19	9.5
SB2C03SA	69	25	12.7
SB2C04SA	69	25	19

Item No. (S. cut)	Size(mm)		
	L	L1	D
SB3C01SA★	50	19	6
SB3C02SA	63	19	9.5
SB3C03SA	69	25	12.7
SB3C04SA	69	25	16
SB3C05SA	76	32	19



Item No. (S. cut)	Size(mm)		
	L	L1	D
SB6C01SA	60	16	9.5
SB6C02SA	66	22	12.7
SB6C03SA	69	25	16
SB6C04SA	69	25	19

Item No. (S. cut)	Size(mm)		
	L	L1	D
SB7C01SA	74	27	9.5
SB7C02SA	76	28	12.7
SB7C03SA	77	30	16
SB7C04SA	85	38	19

Item No. (S. cut)	Size(mm)		
	L	L1	D
SB8C01SA★	50	5	6
SB8C02SA	52	8	9.5
SB8C03SA	55	11	12.7
SB8C04SA	58	14	16
SB8C05SA	62	16	19

SB6SH·SB6S-

■ SUPER CARBIDE BUR SET

► Accessories

- Plastic case as standard acc.



Shank dia. $\phi 6\text{mm}$ (W. cut) 5pcs-set

Set item No.	Set details
SB6SH	SB1C06·SB2C06·SB3C03·SB7C03·SB8C05

Shank dia. $\phi 6\text{mm}$ (W. cut) 10pcs-set

Set item No.	Set details
SB6S1	SB1C06·SB2C06·SB3C03:2pcs/set SB4C03·SB5C04·SB7C03·SB8C05:1pcs/set

Shank dia. $\phi 6\text{mm}$ (W. cut) 10pcs-set

Set item No.	Set details
SB6S2	SB1C06·SB2C06·SB3C03:3pcs/set SB8C05:1pcs/set

Shank dia. $\phi 6\text{mm}$
Diamond Cut



Item No.	Size(mm)		
	L	L1	D
SB1C01D	63	19	9.5

Item No.	Size(mm)		
	L	L1	D
SB2C02D	63	19	9.5

Item No.	Size(mm)		
	L	L1	D
SB3C03D	63	19	9.5