

# Electrically Conductive Castors I –Medium duty type (Steel)–

RoHS compliant products.

## POINT


- Wheels are made of homogeneous electrically conductive material. Long lasting performance even after friction.
- EUW wheel; Made with **carbonless materials**, resulting in non-marking.
- **Electrically conductive grease** in the swivel head.
- Smooth swiveling thanks to **double bearing** in the swivel head.
- EUW wheel comes with **box style structure**.



(Image for reference only.)

## USE EXAMPLE

- For electric parts carriers and precise measuring equipment.
  - For carriers in clean room.
- ©We'll accept your custom-order. Please feel free to contact us.  
(Use "Specification Form for Custom-designed castor" at the end of this catalog.)  
©Please feel free to ask about the product weight for each item.



### J Swivel castors



J-75
J-100
J-130
J-150
J-200

• Color/Finish; Zinc plated

### JB Swivel with stopper (Right)



JB-75
JB-100
JB-130
JB-150
JB-200

### JB(L) Swivel with stopper (Left)



JB-100(L)
JB-130(L)
JB-150(L)
JB-200(L)

### K Fixed castors



K-75
K-100
K-130
K-150
K-200

• Color/Finish; Zinc plated

### KB Fixed with stopper (Right)



KB-75
KB-100
KB-130
KB-150
KB-200

### KB(L) Fixed with stopper (Left)




KB-100(L)
KB-130(L)
KB-150(L)
KB-200(L)

## WHEELS ベアリング変更EUW JBB→CB

JBB ... Radial ball bearing

See P.62 to P.71 for detailed description.



EUW (Antistatic UR) JBB MCD JBB  
 • Volume resistance 10<sup>6</sup>~10<sup>9</sup>Ω·cm\* (Conductive monomer cast nylon)

• Volume resistance 10<sup>2</sup>~10<sup>4</sup>Ω·cm\* \*For reference only, not guaranteed.  
 NB with stopper type: not available.  
 NB φ200: upon request.