



K

- 重量用キャスター
- キャスター
- 双輪キャスター
- 緩衝器付キャスター
- アジャスター付キャスター

- 戸車
- ボールキャスター
- モニターアーム
- レベルアジャスター
- ペダルロック
- ステップ
- スライドレール

低床重荷重用キャスター

SWIVEL AND RIGID CASTERS



K-1508	K-1558	K-508	K-558
ステンレス製 自在車	ステンレス製 固定車	鉄製 自在車	鉄製 固定車

特徴 Feature

- 旋回部分・車軸は表面硬化焼入処理
- 耐油・耐薬品・耐摩耗性・耐熱性(-40~+120℃)に優れたMCナイロン使用
- Swivel head and axletree are hardened.
- MC-nylon is oil-resistant, chemicals-resistant, wear-resistant and heat-resistant (-40°C to +120°C).



K-1508-50




K-558-75



- 仕様 [K-1508・K-1558]
- 材質: 本体/冷間圧延ステンレス鋼板(SUS304) 車輪/MCナイロン(ブルー)
 - 表面仕上: 電解研磨
- [K-508・K-558]
- 材質: 本体/冷間圧延鋼板(SPCC) 車輪/MCナイロン(ブルー)
 - 表面仕上: 本体/焼付塗装(ブラック)
- 用途
- 大型・中型の機器
- 納期
- 標準品・・・納期お問合せ下さい
- 備考
- MCナイロン(ブラック)製もあります。
 - 本体白色塗装もできます。

- Specifications [K-1508・K-1558]
- Material: Main body: Cold rolled stainless steel plate (SUS304) Wheel: MC-nylon (Blue)
 - Finish: Electrolytic machining
- [K-508・K-558]
- Material: Main body: Cold rolled steel plate (SPCC). Wheel: MC-nylon (Blue)
 - Finish: Main body: Baked (Black)
- Specific use
- Large or middle-sized equipment
- Remarks
- MC-nylon (Black) is available.
 - White painting main body is available.

[K-508]



[K-558]



商品番号 Product No.		RoHS		CAD		φD	H	L1×W1	P1×P2 (P1×P2)	L2	W2	t		d	許容荷重kN Allowable load	製品質量(g) Mass		コード Code		単価 Price		量販価格 Bulk Price			
SUS	SPCC	SUS	SPCC	SUS	SPCC							SUS	SPCC			SUS	SPCC	SUS	SPCC	SUS	SPCC	SUS	SPCC	SUS	SPCC
K-1508-50	K-508-50	●	●	3D	2D/3D	50	78	82×82	65×65 (55×55)	18	32.5	3.0	3.2	9.5	2.94	550	610	31675	31024	¥5,600	¥2,100	20個~	¥5,380	20個~	¥2,016
K-1508-65	K-508-65	●	●	3D	2D/3D	65	96.5	100×100	78×78 (63×63)	22	36	4.0	10.5	3.92	980	1,050	31676	31025	¥9,300	¥3,100	12個~	¥8,930	12個~	¥2,980	
K-1508-75	K-508-75	●	●	3D	2D/3D	75	108	100×100	78×78 (63×63)	25	39	4.0	10.5	4.90	1,113	1,190	31677	31026	¥10,500	¥3,800	12個~	¥10,100	12個~	¥3,650	

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。 ※大量のご注文は更にお安くなります。

商品番号 Product No.		RoHS		CAD		φD	H	L×W1	P1×P2	W2	t		φd	許容荷重kN Allowable load	製品質量(g) Mass		コード Code		単価 Price		量販価格 Bulk Price			
SUS	SPCC	SUS	SPCC	SUS	SPCC						SUS	SPCC			SUS	SPCC	SUS	SPCC	SUS	SPCC	SUS	SPCC	SUS	SPCC
K-1558-50	K-558-50	●	●	3D	2D/3D	50	78	85×58	55×28	32.5	3.0	3.2	9.5	2.94	360	370	31678	31027	¥3,500	¥1,600	20個~	¥3,360	20個~	¥1,536
K-1558-65	K-558-65	●	●	3D	2D/3D	65	96.5	86×59	55×28	36	4.0	10.5	3.92	620	590	31679	31028	¥4,100	¥2,300	12個~	¥3,940	12個~	¥2,208	
K-1558-75	K-558-75	●	●	3D	2D/3D	75	108	95×72	63×40	39	4.0	10.5	4.90	780	750	31680	31029	¥4,600	¥2,900	12個~	¥4,420	12個~	¥2,784	

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。 ※大量のご注文は更にお安くなります。