



Stock 38,650 Items

Soft Jaw (for HOWA)




- Features**
- S45C steel which is easy to modify and has suitable hardness is used.
 - Careful processing has been given considering points such as lowering of restoration accuracy (Core run out) after reinstallation and factors causing attachment distortion of the Master Jaw.
- Origin**
- Japan

For HO1MA

Order Unit: 1 Set

TRUSCO NAKAYAMA CORPORATION


| Order Code | Item No. | Price (per set) | MSRP (per set) | Chuck Outer Diameter (inch) | Pitch (mm) | Length (mm) | Width (mm) | Height (mm) | SPQ (set) | Weight (kg/set) |
|------------|--------------|-----------------|----------------|-----------------------------|------------|-------------|------------|-------------|-----------|-----------------|
| 114-0574 | HO1MA-4-1.5 | ¥ 4,370 | ¥ 4,720 | 4 | 1.5 | 54.0 | 23 | 25 | 1 | 0.60 |
| 114-0582 | HO1MA-5-1.5 | ¥ 4,370 | ¥ 4,720 | 5 | 1.5 | 58.5 | 23 | 25 | 1 | 0.65 |
| 114-0591 | HO1MA-6-1.5 | ¥ 4,842 | ¥ 5,230 | 6 | 1.5 | 72.0 | 31 | 40 | 1 | 1.70 |
| 114-0604 | HO1MA-6-3.0 | ¥ 4,842 | ¥ 5,230 | 6 | 3.0 | 72.0 | 31 | 40 | 1 | 1.70 |
| 114-0612 | HO1MA-8-1.5 | ¥ 5,471 | ¥ 5,910 | 8 | 1.5 | 90.0 | 34 | 40 | 1 | 2.30 |
| 114-0621 | HO1MA-8-3.0 | ¥ 5,471 | ¥ 5,910 | 8 | 3.0 | 90.0 | 34 | 40 | 1 | 2.30 |
| 114-0639 | HO1MA-10-1.5 | ¥ 6,776 | ¥ 7,320 | 10 | 1.5 | 110.0 | 40 | 40 | 1 | 3.50 |
| 114-0647 | HO1MA-10-3.0 | ¥ 6,776 | ¥ 7,320 | 10 | 3.0 | 110.0 | 40 | 40 | 1 | 3.50 |
| 114-0655 | HO1MA-12-1.5 | ¥ 9,683 | ¥ 10,460 | 12 | 1.5 | 129.0 | 50 | 50 | 1 | 6.70 |
| 114-0663 | HO1MA-12-3.0 | ¥ 9,683 | ¥ 10,460 | 12 | 3.0 | 129.0 | 50 | 50 | 1 | 6.70 |
| 114-0671 | HO1MA-15-3.0 | ¥ 27,698 | ¥ 29,920 | 15 | 3.0 | 156.0 | 64 | 70 | 1 | 13.60 |



For HO7MA

Order Unit: 1 Set


| Order Code | Item No. | Price (per set) | MSRP (per set) | Chuck Outer Diameter (inch) | Pitch (mm) | Length (mm) | Width (mm) | Height (mm) | SPQ (set) | Weight (kg/set) |
|------------|----------|-----------------|----------------|-----------------------------|------------|-------------|------------|-------------|-----------|-----------------|
| 114-0787 | HO7MA-6 | ¥ 5,406 | ¥ 5,840 | 6 | 1.5 | 70.5 | 30 | 30 | 1 | 1.2 |
| 114-0795 | HO7MA-8 | ¥ 6,582 | ¥ 7,110 | 8 | 1.5 | 90.0 | 32 | 35 | 1 | 1.9 |
| 114-0809 | HO7MA-10 | ¥ 8,248 | ¥ 8,910 | 10 | 1.5 | 90.0 | 35 | 40 | 1 | 2.4 |
| 114-0817 | HO7MA-12 | ¥ 13,515 | ¥ 14,600 | 12 | 1.5 | 105.0 | 40 | 50 | 1 | 4.2 |



For HO7MA (high jaw)

Order Unit: 1 Set


| Order Code | Item No. | Price (per set) | MSRP (per set) | Chuck Outer Diameter (inch) | Pitch (mm) | Length (mm) | Width (mm) | Height (mm) | SPQ (set) | Weight (kg/set) |
|------------|-------------|-----------------|----------------|-----------------------------|------------|-------------|------------|-------------|-----------|-----------------|
| 112-9571 | HO7MA-8-60 | ¥ 9,850 | ¥ 10,640 | 8 | 1.5 | 90 | 32 | 60 | 1 | 3.3 |
| 112-9589 | HO7MA-8-90 | ¥ 14,700 | ¥ 15,880 | 8 | 1.5 | 90 | 32 | 90 | 1 | 5.4 |
| 112-9597 | HO7MA-10-60 | ¥ 14,534 | ¥ 15,700 | 10 | 1.5 | 90 | 35 | 60 | 1 | 3.6 |
| 112-9601 | HO7MA-10-90 | ¥ 19,699 | ¥ 21,280 | 10 | 1.5 | 90 | 35 | 90 | 1 | 5.3 |



For HO22M

Order Unit: 1 Set


| Order Code | Item No. | Price (per set) | MSRP (per set) | Chuck Outer Diameter (inch) | Pitch (mm) | Length (mm) | Width (mm) | Height (mm) | SPQ (set) | Weight (kg/set) |
|------------|----------|-----------------|----------------|-----------------------------|------------|-------------|------------|-------------|-----------|-----------------|
| 114-0833 | HO22M-6 | ¥ 5,498 | ¥ 5,940 | 6 | 1.5 | 70.5 | 30 | 30 | 1 | 1.2 |
| 114-0841 | HO22M-8 | ¥ 8,461 | ¥ 9,140 | 8 | 1.5 | 90.0 | 35 | 40 | 1 | 2.4 |



For HO24M (two direction)

Order Unit: 1 Set

| Order Code | Item No. | Price (per set) | MSRP (per set) | Chuck Outer Diameter (inch) | Pitch (mm) | Length (mm) | Width (mm) | Height (mm) | SPQ (set) | Weight (kg/set) |
|------------|----------|-----------------|----------------|-----------------------------|------------|-------------|------------|-------------|-----------|-----------------|
| 114-0680 | HO24M-6 | ¥ 4,295 | ¥ 4,640 | 6 | 1.5 | 70.5 | 30 | 30 | 1 | 0.84 |
| 114-0698 | HO24M-8 | ¥ 6,517 | ¥ 7,040 | 8 | 1.5 | 90.0 | 35 | 40 | 1 | 1.67 |
| 114-0701 | HO24M-10 | ¥ 10,747 | ¥ 11,610 | 10 | 1.5 | 105.0 | 40 | 50 | 1 | 2.78 |



For HO27M

Order Unit: 1 Set

| Order Code | Item No. | Price (per set) | MSRP (per set) | Chuck Outer Diameter (inch) | Pitch (mm) | Length (mm) | Width (mm) | Height (mm) | SPQ (set) | Weight (kg/set) |
|------------|----------|-----------------|----------------|-----------------------------|------------|-------------|------------|-------------|-----------|-----------------|
| 114-0868 | HO27M-6 | ¥ 6,628 | ¥ 7,160 | 6 | 1.5 | 66.5 | 35 | 35 | 1 | 1.5 |
| 114-0876 | HO27M-8 | ¥ 7,480 | ¥ 8,080 | 8 | 1.5 | 85.5 | 40 | 40 | 1 | 2.5 |
| 114-0884 | HO27M-10 | ¥ 10,646 | ¥ 11,500 | 10 | 1.5 | 108.0 | 45 | 45 | 1 | 4.3 |
| 114-0892 | HO27M-12 | ¥ 12,885 | ¥ 13,920 | 12 | 1.5 | 111.0 | 50 | 60 | 1 | 6.4 |



Contact us: 0120-509-849 <http://www.orange-book.com/>