



## SB-A-(E·ES·S)·SB-B-(E·ES·S)·SB-D-(S) ■ SUPER CARBIDE BUR

Shank diameter φ3mm (All carbide)

Shape	Item No. (W. cut)	Item No. (S. cut)	Size(mm)		
			L	L1	D
	SB1A01	SB1A01S	38	6	1.5
	SB1A02	SB1A02S	38	11	2.5
	SB1A03	SB1A03S	38	14	3
	SB1A01E	SB1A01ES	38	14	3
	SB2A01	SB2A01S	38	11	2.5
	SB2A02	SB2A02S	38	14	3
	SB3A01	SB3A01S	38	12.7	3
	SB3A02	SB3A02S	38	6	3
	SB4A01	SB4A01S	38	9.5	3
	SB4A02	SB4A02S	38	6	3
	SB4A03	SB4A03S	38	12.7	3
	SB5A01	SB5A01S	38	16	3 <sup>7</sup>
	SB5A02	SB5A02S	38	8.9	3 <sup>12</sup>
	SB5A03	SB5A03S	38	11	3 <sup>14</sup>
	SB6A01	SB6A01S	38	5.5	3
	SB7A01	SB7A01S	38	12.7	3 <sup>8</sup>
	SB7A02	SB7A02S	38	9.5	3 <sup>8</sup>
	SB8A01	SB8A01S	38	2.3	2.5
	SB8A02	SB8A02S	38	2.5	3
	SB49A01	SB49A01S	38	1.5	3 <sup>90</sup>
	SB50A01	SB50A01S	38	2.5	3 <sup>60</sup>
	SB51A01	SB51A01S	38	6.3	3
	SB52A01	SB52A01S	38	4	3 <sup>10</sup>

Shank diameter φ3mm (All carbide)

Shape	Item No. (W. cut)	Item No. (S. cut)	Size(mm)		
			L	L1	D
	SB1D01	SB1D01S	38	12.7	4
	SB1D02	SB1D02S	38	12.7	5
	SB2D03	SB2D03S	38	12.7	4
	SB2D04	SB2D04S	38	12.7	5
	SB3D08	SB3D08S	38	12.7	5
	SB4D09	SB4D09S	38	12.7	5
	SB5D12	SB5D12S	38	12.7	5 <sup>16</sup>
	SB6D07	SB6D07S	38	7.1	5
	SB7D11	SB7D11S	38	12.7	5 <sup>14</sup>
	SB8D05	SB8D05S	38	3.4	4
	SB8D06	SB8D06S	38	4.7	5
	SB51D10	SB51D10S	38	9.5	5
	SB52D13	SB52D13S	38	6.3	5 <sup>10</sup>

Shank diameter φ3mm

Shape	Item No. (W. cut)	Item No. (S. cut)	Size(mm)		
			L	L1	D
	SB1B01	SB1B01S	50	12.7	6.3
	SB1B02E	SB1B02ES	43	4.7	6.3
	SB2B03	SB2B03S	50	12.7	6.3
	SB3B06	SB3B06S	50	12.7	6.3
	SB4B07	SB4B07S	50	12.7	6.3
	SB5B08	SB5B08S	54	12.7	6.3 <sup>22</sup>
	SB6B05	SB6B05S	47	9.5	6.3
	SB8B04	SB8B04S	44	5	6.3
	SB52B09	SB52B09S	44	6	6.3 <sup>10</sup>