

Belt Punches

The number next to the logo mark indicates items in stock for each brand.

Hammers • Punches

Single-Ended Hammers

Double-Ended Hammers

Combination Hammers

Shock-Less Hammers

Resin Hammers-Rubber Hammers

Nonferrous Hammers

Stainless Steel Hammers

Wood Hammers

Stone Hammers

Welding Hammers

Sheet Metal Hammers

Claw Hammers

Centering Hammers

Hammers for Woodwork

Hammers for Electric Work

Test Hammers

Wedges

Grip Tapes

Bars

Chisels

Stamps


Date Marks

Industrial Stamps

Punches

TRUSCO **Stock 38,650 Items**


Belt Punch




- Features**
- Cuts well because the blade edges are made thin.
 - Shape that easily produces scraps.
 - Sharpness and cost are compatible at high level by the special quenching process.
- Use**
- Drilling into belts, leather, vinyl, rubber, paper, cloth and so on.
- Specs**
- Black Dye (parker finishing)
- Materials**
- Carbon Steel
- Origin**
- Japan

Warning

- Can not be used for drilling metal.
- Dimensional errors are somewhat caused by the material and the thickness of the material to be cut.



Used for drilling rubber, paper, leather, cloth etc.



Order Unit: 1 Piece (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Piece (Price revision date: Jan, 2016)

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Hole Diameter (mm)	Total Length (mm)	Outer Diameter (mm)	SPQ (piece)	Weight (kg)	Order Code	Item No.	Price (per piece)	MSRP (per piece)	Hole Diameter (mm)	Total Length (mm)	Outer Diameter (mm)	SPQ (piece)	Weight (kg)
336-4518	TPO-10	¥ 334	¥ 360	1.0	85	6	10	0.012	336-4771	TPO-250	¥ 2,509	¥ 2,710	25.0	100	30	10	0.290
336-4526	TPO-15	¥ 334	¥ 360	1.5	85	6	10	0.012	336-4780	TPO-260	¥ 2,916	¥ 3,150	26.0	120	32	1	0.360
336-4534	TPO-20	¥ 314	¥ 340	2.0	85	6	10	0.012	336-4798	TPO-270	¥ 3,036	¥ 3,280	27.0	120	32	1	0.365
336-4542	TPO-25	¥ 314	¥ 340	2.5	85	6	10	0.012	336-4801	TPO-280	¥ 3,194	¥ 3,450	28.0	125	34	1	0.400
336-4551	TPO-30	¥ 314	¥ 340	3.0	85	6	10	0.016	336-4810	TPO-290	¥ 3,416	¥ 3,690	29.0	125	35	1	0.425
336-4569	TPO-40	¥ 314	¥ 340	4.0	85	7	10	0.020	336-4828	TPO-300	¥ 3,582	¥ 3,870	30.0	125	35	1	0.415
336-4577	TPO-50	¥ 314	¥ 340	5.0	85	8	10	0.026	336-4836	TPO-310	¥ 3,768	¥ 4,070	31.0	125	38	1	0.550
336-4585	TPO-60	¥ 314	¥ 340	6.0	90	9	10	0.034	336-4844	TPO-320	¥ 4,137	¥ 4,470	32.0	125	38	1	0.540
336-4593	TPO-70	¥ 314	¥ 340	7.0	90	10	10	0.041	336-4852	TPO-330	¥ 4,416	¥ 4,770	33.0	130	38	1	0.575
336-4607	TPO-80	¥ 370	¥ 400	8.0	90	11	10	0.048	336-4861	TPO-340	¥ 4,601	¥ 4,970	34.0	130	42	1	0.655
336-4615	TPO-90	¥ 417	¥ 450	9.0	90	12	10	0.054	336-4879	TPO-350	¥ 4,850	¥ 5,240	35.0	130	42	1	0.645
336-4623	TPO-100	¥ 518	¥ 560	10.0	90	13	10	0.062	336-4887	TPO-360	¥ 5,156	¥ 5,570	36.0	130	42	1	0.630
336-4631	TPO-110	¥ 602	¥ 650	11.0	95	15	10	0.087	336-4895	TPO-370	¥ 5,350	¥ 5,780	37.0	130	45	1	0.700
336-4640	TPO-120	¥ 703	¥ 760	12.0	100	16	10	0.100	336-4909	TPO-380	¥ 5,610	¥ 6,060	38.0	130	45	1	0.680
336-4658	TPO-130	¥ 759	¥ 820	13.0	100	17	10	0.110	336-4917	TPO-390	¥ 5,980	¥ 6,460	39.0	135	48	1	0.890
336-4666	TPO-140	¥ 944	¥ 1,020	14.0	100	17	10	0.130	336-4925	TPO-400	¥ 6,341	¥ 6,850	40.0	135	48	1	0.820
336-4674	TPO-150	¥ 1,047	¥ 1,130	15.0	100	20	10	0.150	336-4933	TPO-410	¥ 6,702	¥ 7,240	41.0	135	48	1	0.915
336-4682	TPO-160	¥ 1,102	¥ 1,190	16.0	100	20	10	0.145	336-4941	TPO-420	¥ 6,934	¥ 7,490	42.0	135	50	1	0.920
336-4691	TPO-170	¥ 1,221	¥ 1,320	17.0	100	21	10	0.155	336-4950	TPO-430	¥ 7,082	¥ 7,650	43.0	135	50	1	0.920
336-4704	TPO-180	¥ 1,286	¥ 1,390	18.0	100	22	10	0.160	336-4968	TPO-440	¥ 7,489	¥ 8,090	44.0	135	54	1	1.100
336-4712	TPO-190	¥ 1,398	¥ 1,510	19.0	100	23	10	0.175	336-4976	TPO-450	¥ 7,989	¥ 8,630	45.0	135	54	1	1.035
336-4721	TPO-200	¥ 1,620	¥ 1,750	20.0	100	25	10	0.210	336-4984	TPO-460	¥ 8,590	¥ 9,280	46.0	140	54	1	1.020
336-4739	TPO-210	¥ 1,759	¥ 1,900	21.0	100	25	10	0.210	336-4992	TPO-470	¥ 9,044	¥ 9,770	47.0	140	57	1	1.000
336-4747	TPO-220	¥ 1,962	¥ 2,120	22.0	100	27	10	0.235	336-5000	TPO-480	¥ 9,396	¥ 10,150	48.0	140	57	1	1.260
336-4755	TPO-230	¥ 2,148	¥ 2,320	23.0	100	28	10	0.235	336-5018	TPO-490	¥ 9,813	¥ 10,600	49.0	140	60	1	1.300
336-4763	TPO-240	¥ 2,343	¥ 2,530	24.0	100	30	10	0.300	336-5026	TPO-500	¥ 10,368	¥ 11,200	50.0	140	60	1	1.235



Punch Table Materials • Polyethylene

Order Unit: 1 Sheet

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Vertical (mm)	Horizontal (mm)	Thickness (mm)	SPQ (sheet)	Weight (kg)
490-1819	TPO-S	¥ 1,666	¥ 1,800	100	150	10	40	0.155

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Punch Set



- Features**
- Cuts well because the blade edges are made thin.
 - Shape that easily produces scraps.
 - Convenient for storage and management as frequently used sizes are collected up.
 - Sharpness and cost are compatible at high level by the special quenching process.
- Use**
- Drilling into belts, leather, vinyl, rubber, paper, cloth and so on.
- Specs**
- Black Dye (parker finishing)
- Materials**
- Carbon Steel
- Origin**
- Japan

Warning

- Can not be used for drilling metal.
- Dimensional errors are somewhat caused by the material and the thickness of the material to be cut.

Order Unit: 1 Set

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents (mm)	Set Contents (piece)	SPQ (set)	Weight (kg/set)
336-5034	TPO-55	¥ 1,962	¥ 2,120	5, 6, 8, 9, 13	5	1	0.28
336-5042	TPO-85	¥ 2,343	¥ 2,530	3, 4, 5, 6, 7, 8, 9, 10	8	1	0.31
336-5051	TPO-115	¥ 18,051	¥ 19,500	3, 5, 6, 8, 9, 11, 13, 16, 19, 22, 25	11	1	2.10

Contact us:0120-509-849 <http://www.orange-book.com/>