




Stock
38,650
Items

"Universal Design Standard Caliper"

Repairing
OK

Calibration OK
Approx. 2 Weeks

RoHS



THN-15-U

Features

- A standard caliper of universal design.
- By making the step scale and the numbers to universal letters, the visibility of the scale is greatly improved.
- The vernier integral type makes the scale easier to see.
- Has a silver finish.

Use

- For outer measurement, inner measurement, depth measurement, step difference measurement.

Origin

- China



Example



Adopted universal design character

1234567890 ▶ 1234567890

Characters used in existing items

Universal Design Character

Improved readability of measured numerical values.

Order Unit: 1 Piece

(Price revision date: Jan, 2018)

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Measurement Range (mm)	Instrument Error (mm)	Minimum Display (mm)	Outer Side Jaws (mm)	Interior Jaws (mm)	Depth Bar	SPQ (piece)	Weight (g)
415-3006	THN-10-U	¥ 4,066	¥ 5,020	0 to 100	±0.05	0.05	40.0	16	Yes	1	130
415-3014	THN-15-U	¥ 4,066	¥ 5,020	0 to 150	±0.05	0.05	40.0	16	Yes	1	140
415-3022	THN-20-U	¥ 5,646	¥ 6,970	0 to 200	±0.05	0.05	50.0	17	Yes	1	210
415-3031	THN-30-U	¥ 10,579	¥ 13,060	0 to 300	±0.08	0.05	64.0	20	Yes	1	380

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock
38,650
Items

Standard Type Caliper

Repairing
OK

Calibration OK
Approx. 2 Weeks

RoHS



THN-15

Features

- The vernier integral type makes the scale easier to see.
- Has a silver finish.

Use

- For outer measurement, inner measurement, depth measurement, step difference measurement.

Origin

- China


Order Unit: 1 Piece

(Price revision date: Jan, 2018)

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Measurement Range (mm)	Instrument Error (mm)	Minimum Display (mm)	Outer Side Jaws (mm)	Interior Jaws (mm)	Depth Bar	SPQ (piece)	Weight (g)
415-0881	THN-10	¥ 4,066	¥ 5,020	0 to 100	±0.05	0.05	40.0	16	Yes	1	130
415-0899	THN-15	¥ 4,066	¥ 5,020	0 to 150	±0.05	0.05	40.0	16	Yes	1	140
415-0902	THN-20	¥ 5,646	¥ 6,970	0 to 200	±0.05	0.05	50.0	17	Yes	1	210
415-0911	THN-30	¥ 10,579	¥ 13,060	0 to 300	±0.08	0.05	64.0	20	Yes	1	380

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock
56
Items

Vernier Caliper with Analog Display



Repairing
OK

Calibration OK
Approx. 4 weeks



16FN

Features

- Vernier and main scale have a satin chrome finish to prevent reflection for reading.

Use

- For outer diameter measurement, inner diameter measurement, step difference measurement, and depth measurement.

Accessories

- Screw size table

Origin

- China

Order Unit: 1 Piece

MAHR JAPAN

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Manufacturer Code	Measurement Range (mm)	Instrument Error (mm)	Minimum Display (mm)	Outer Side Jaws (mm)	Interior Jaws (mm)	Depth Bar	SPQ (piece)	Weight (g)
835-3816	16FN	¥ 5,468	¥ 5,400	4100420	0 to 150	0.05	0.05	40	16	Yes	1	322
835-3817	16GN	¥ 7,493	¥ 7,400	4100650	0 to 150	0.04	0.02	40	16	Yes	1	322

Contact us: 045-540-3591 <http://www.mahr.jp/>



Stock
1,103
Items

Digital Caliper (for left-handed)

Repairing
OK

Calibration OK
Approx. 2 Weeks



THL-150

Outer Side Jaws

Features

- Developed for left-handed persons.

Use

- For outer measurement, inner measurement, step difference measurement, and depth measurement.

Origin

- China

SPQ: 1 Piece

Order Unit: 1 Piece

(Price revision date: Jun, 2015) NIIGATASEIKI Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Manufacturer Code	Measurement Range (mm)	Instrument Error (mm)	Minimum Display (mm)	Outer Side Jaws (mm)	Interior Jaws (mm)	Depth Bar	Weight (g)
377-6611	THL-150	¥ 11,880	¥ 11,000	151321	0 to 150	±0.05	0.05	40	16	Yes	150

Contact us: 0256-31-5660 <http://www.sokuteikougu.com/>