


● SERVICE CONDITIONS

Max. Pressure : 13.7MPa (140kgf/cm²)
 Max. Temperature : 100°C
 Material : Steel (Weld Steel)
 Seal : NBR
 Connection : Female Taper Thread (Rc)


● DESCRIPTION OF B series: Example for placing order

Type→Style No.→Size
 B → 1/2/3 → 10A/15A/20A/25A/32A/40A
 Example: B-1 25A
 * As to B series, PTFE or FKM seals are available for higher temperatures or chemical products .


Style No.1



Style No.2



Style No.3




DIMENSIONS OF B series

Nominal Size		A	B	C	D	E	F	G
10A	3/8B	91	77	73	(48)	32	32	49
15A	1/2B	91	77	73	(48)	32	32	49
20A	3/4B	118	108	107.5	(66)	46	46	63
25A	1B	118	108	107.5	(66)	46	46	63
32A	1 1/4B	120	130	135	(72)	58	58	45
40A	1 1/2B	120	134	145	(78)	63	63	52

* in () : reference dimensions

B series DYNAMIC TORQUE GRAPH



* Refer to Page 14.