

Total 325 models

Unit (mm)

Model Number	Radius of Ball Nose R	Effective Length ℓ_e	Length of Cut ℓ	Neck Diameter ϕ_d	Shank Taper Angle Bta	Overall Length L	Shank Diameter ϕ_d	Suggested Retail Price ¥	Effective Length by Inclined Angles				
									30°	1°	1°30'	2°	3°
CSELB 2001-002	RO.05	0.2	0.08	0.095	11°	45	4	11,630	0.22	0.24	0.26	0.28	0.31
CSELB 2001-003		0.3				45	4	11,630	0.33	0.35	0.38	0.40	0.45
CSELB 2001-005		0.5				45	4	12,540	0.54	0.58	0.61	0.64	0.72
CSELB 20015-003	RO.075	0.3	0.12	0.135	11°	45	4	13,450	0.36	0.38	0.40	0.42	0.48
CSELB 20015-005		0.5				45	4	14,250	0.58	0.60	0.63	0.67	0.75
CSELB 20015-010		1				45	4	14,820	1.10	1.15	1.21	1.28	1.43
CSELB 2002-003	RO.1	0.3	0.16	0.19	11°	45	4	8,090	0.40	0.42	0.44	0.46	0.52
CSELB 2002-005		0.5				45	4	8,090	0.61	0.64	0.67	0.71	0.79
CSELB 2002-005-6		0.5				50	6	11,290	0.61	0.64	0.67	0.71	0.79
CSELB 2002-0075		0.75				45	4	8,090	0.87	0.92	0.96	1.01	1.13
CSELB 2002-010		1				45	4	8,090	1.14	1.19	1.25	1.32	1.48
CSELB 2002-010-6		1				50	6	11,290	1.14	1.19	1.25	1.32	1.48
CSELB 2002-0125		1.25				45	4	8,780	1.39	1.45	1.53	1.61	1.80
CSELB 2002-015		1.5				45	4	8,780	1.65	1.73	1.81	1.91	2.14
CSELB 2002-015-6		1.5				50	6	12,250	1.65	1.73	1.81	1.91	2.14
CSELB 2002-0175		1.75				45	4	9,690	1.91	2.00	2.10	2.22	2.49
CSELB 2002-020		2				45	4	9,690	2.17	2.28	2.39	2.52	2.83
CSELB 2002-020-6		2				50	6	13,520	2.17	2.28	2.39	2.52	2.83
CSELB 2002-0225		2.25				45	4	10,600	2.43	2.55	2.68	2.83	3.17
CSELB 2002-025		2.5				45	4	10,600	2.69	2.83	2.97	3.13	3.51
CSELB 2002-030		3				45	4	11,400	3.22	3.37	3.55	3.74	4.20
CSELB 2003-005	RO.15	0.5	0.24	0.29	11°	45	4	7,980	0.61	0.64	0.67	0.70	0.77
CSELB 2003-006		0.6				45	4	7,980	0.71	0.75	0.78	0.82	0.91
CSELB 2003-0075		0.75				45	4	7,980	0.87	0.91	0.95	1.00	1.12
CSELB 2003-010		1				45	4	7,980	1.13	1.19	1.24	1.31	1.46
CSELB 2003-010-6		1				50	6	10,830	1.13	1.19	1.24	1.31	1.46
CSELB 2003-0125		1.25				45	4	8,550	1.38	1.45	1.52	1.60	1.78
CSELB 2003-015		1.5				45	4	8,550	1.64	1.72	1.81	1.90	2.12
CSELB 2003-015-6		1.5				50	6	11,860	1.64	1.72	1.81	1.90	2.12
CSELB 2003-0175		1.75				45	4	8,550	1.91	2.00	2.10	2.21	2.47
CSELB 2003-020		2				45	4	8,550	2.17	2.27	2.38	2.51	2.81
CSELB 2003-020-6		2				50	6	11,860	2.17	2.27	2.38	2.51	2.81
CSELB 2003-0225		2.25				45	4	8,780	2.43	2.55	2.67	2.82	3.15
CSELB 2003-025		2.5				45	4	8,780	2.69	2.82	2.96	3.12	3.49
CSELB 2003-030		3				45	4	8,780	3.22	3.37	3.54	3.73	4.18
CSELB 2003-040		4				45	4	9,120	4.26	4.47	4.70	4.95	5.55
CSELB 2003-050		5				45	4	10,260	5.31	5.57	5.85	6.17	6.92

Next Page ➡