


WP dimensions

DXF/DWG/PDF/STP drawings available on our website.



Product no. / Dimensions

Product no.		IP Code	External dimensions			Internal dimensions			Screw	Recommended torque (N · m)	Weight (g)
● White gray (ASA)	● Charcoal gray (ABS)		W	D	H	w	d	h			
WP 5- 7-2G	WP 5- 7-2C	IP68	52	65	18	46	37	13	M2-8 × 4pcs	0.2 ~ 0.25	31.5
WP 5- 7-3G	WP 5- 7-3C	IP68	52	65	27	45	36.5	22	M2-8 × 4pcs	0.2 ~ 0.25	39.5
WP 6- 8-2G	WP 6- 8-2C	IP68	60	80	20	53.5	52	14.7	M2-8 × 4pcs	0.25 ~ 0.3	41.5
WP 6- 8-3G	WP 6- 8-3C	IP68	60	80	30	53	51	24.7	M2-8 × 4pcs	0.25 ~ 0.3	49
WP 8- 8-2G	WP 8- 8-2C	IP68	75	75	22	67	42	16.4	M2.5-8 × 4pcs	0.25 ~ 0.35	57.5
WP 8- 8-4G	WP 8- 8-4C	IP68	75	75	35	66	42	29.4	M2.5-16 × 4pcs	0.25 ~ 0.35	88.5
WP 8-10-2G	WP 8-10-2C	IP68	75	100	22	67	67	16	M2.5-8 × 4pcs	0.25 ~ 0.35	74
WP 8-10-4G	WP 8-10-4C	IP68	75	100	35	66	67	29	M2.5-16 × 4pcs	0.25 ~ 0.35	95
WP 9-13-3G	WP 9-13-3C	IP68	90	130	25	81	91	18	M2.5-8 × 6pcs	0.25 ~ 0.35	113
WP 9-13-4G	WP 9-13-4C	IP68	90	130	40	81	91	33	M2.5-16 × 6pcs	0.25 ~ 0.35	141
WP10-10-3G	WP10-10-3C	IP68	100	100	25	90	61	18	M2.5-8 × 4pcs	0.25 ~ 0.35	96
WP10-10-4G	WP10-10-4C	IP68	100	100	40	90	61	33	M2.5-16 × 4pcs	0.25 ~ 0.35	121
WP11-15-3G	WP11-15-3C	IP68	110	150	27	100	110	20	M2.5-8 × 6pcs	0.25 ~ 0.35	153
WP11-15-4G	WP11-15-4C	IP68	110	150	40	100	110	33	M2.5-16 × 6pcs	0.25 ~ 0.35	181
WP13-18-3G	WP13-18-3C	IP68	130	175	30	120	135	23	M2.5-8 × 6pcs	0.25 ~ 0.35	225
WP13-18-5G	WP13-18-5C	IP68	130	175	45	120	135	38	M2.5-16 × 6pcs	0.25 ~ 0.35	266
WP15-15-4G	WP15-15-4C	IP68	150	150	40	141	100	33.5	M3-8 × 4pcs	0.35 ~ 0.45	239
WP15-15-6G	WP15-15-6C	IP68	150	150	55	140	100	48.5	M3-8 × 4pcs	0.35 ~ 0.45	282.5
WP15-21-4G	WP15-21-4C	IP68	150	210	40	141	160	33.5	M3-8 × 6pcs	0.35 ~ 0.45	323
WP15-21-6G	WP15-21-6C	IP68	150	210	55	140	160	48.5	M3-8 × 6pcs	0.35 ~ 0.45	367.5
WP20-20-5G	WP20-20-5C	IP68	200	200	45	190	150	38.5	M3-8 × 8pcs	0.45 ~ 0.55	446
WP20-20-7G	WP20-20-7C	IP68	200	200	65	189	149	58.5	M3-8 × 8pcs	0.45 ~ 0.55	524.5
WP20-28-5G	WP20-28-5C	IP67	200	280	45	190	230	38.5	M3-8 × 8pcs	0.45 ~ 0.55	557.5
WP20-28-7G	WP20-28-7C	IP67	200	280	65	189	229	58.5	M3-8 × 8pcs	0.45 ~ 0.55	646

Recommended torque listed is for reference only; actual may differ. Assemble after testing torque.

Accessories (Optional parts)



Pole mount bracket WPMB series
See page 21



Rubber feet PFRF series
See page 22



TORX screw MR series
See page 22



PCB mounting screw EM series
See page 123



Protective vent PMF series
See page 325 ~ 326



Cable gland
See page 333 ~ 340



Pole mounting belt PKB-10 series
See page 324



Tapping standoff TPS series
See page 122