




K TYPE



UWK-150



● Description of product number

UW K - 150

Wheel type
Bracket type
Wheel diameter

Bracket = Trivalent unichrome coating

Product number	Wheels								
		Wheel diameter D(mm)	Wheel width W(mm)	Mounting height H(mm)	Mounting base A × B(mm)	Mounting dimensions X × Y(mm)	Hole diameter P(mm)	Allowance load daN(kgf)	Wheel weight (g)
W	K-75	75	32	103	95 × 72	63 × 40	9.5	80(81.6)	430
UW								120(122.4)	540
GU								100(102.0)	390
W	K-100	100	32	144	115 × 80	80 × 45	11	120(122.4)	700
NR								100(102.0)	770
UW								180(183.6)	930
GU								100(102.0)	760
W	K-130	130	40	177	137 × 93	100 × 56	11	180(183.6)	1490
NR								180(183.6)	1090
UW			35					250(255.0)	1630
GU		40	180(183.6)	1345					
W	K-150	150	40	198	137 × 93	100 × 56	11	200(204.0)	1650
NR								200(204.0)	1210
UW			38					300(306.0)	1910
GU		40	200(204.0)	1570					
W	K-200	200	43	250	151 × 102	112 × 63	11.5	250(255.0)	3060
UW			42					400(408.0)	3230
GU			43					250(255.0)	2540

- The axle diameter of the rubber wheel with nylon wheel assembly (including B) having wheel diameter of ϕ 130 and ϕ 150 is ϕ 12.
- The rubber wheel with conductive steel plate wheel assembly (including B) having wheel diameter of ϕ 100 and ϕ 150 can be manufactured.
- The urethane wheel with antistatic steel wheel plate assembly (including B) having wheel diameter of ϕ 100 to ϕ 200 can be manufactured.

Wheel in use


Refer to P153 for detailed specifications.



W
Rubber wheel with steel plate wheel assembly (including B)



NR
Rubber wheel with nylon wheel assembly (including B)



UW
Urethane wheel with steel plate wheel assembly (including B)



GU
Urethane wheel with nylon wheel assembly (including B)

J

PM

J2

RJ2

SJ

S

E

G

L

SA

H

CAL -H

M

PL

Silence

SUS -J2

SUS -SJ

SUS -S

SUS -E

SUS -H

P

SKY

Equipped with adjuster foot

Special

Easy lock

Wheels

Wheels

Wheels