


Prices displayed include 8% tax.

TRUSCO Stock 38,650 Items **G Type Grip Pliers**



- Features** • Optimum for sheet metal, welding works and tight fixing of clad plate.
- Specs** • Full Hardened Product: Head Hardness HRC35 to 45, Body Hardness HRC35 to 40
- Materials** • Special Steel
- Origin** • China



For Angle Welding

For Replacement Springs, see p. 4-1765

Opening (mm)			
Square Timber		Pipe	
Min	Max	Min	Max
1	50	φ38	φ64

Order Unit: 1 Piece (Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Max Clamping Pressure (kN)	SPQ (piece)	Weight (g)
253-5165	TGPG-250	¥1,944	¥2,100	266	1.5	1	790

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items **G Type Grip Pliers**



- Features** • Optimum for angle, sheet metal, welding work and tight fixing of clad plate.
- Specs** • Head hardness: HRC40 to 50
- Materials** • Special Steel
- Origin** • China



For Replacement Springs, see p. 4-1765

Opening (mm)			
Square Timber		Pipe	
Min	Max	Min	Max
1	70	φ1	φ80


Order Unit: 1 Piece (Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Max Clamping Pressure (kN)	SPQ (piece)	Weight (g)
374-7247	TVPG-280	¥3,147	¥3,400	297	2.5	1	915

Contact us: 0120-509-849 <http://www.orange-book.com/>

Strong Hand Tools Stock 51 Items **"U Type Grip Plier"**

- Features** • Suitable for holding pipes.
- Materials** • Carbon steel (S45C)
- Chromium molybdenum steel (SCM440)
- Origin** • China




Order Unit: 1 Piece Strong Hand Tools

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Max Opening (mm)	SPQ (piece)	Weight (g)
835-8181	PUP90	¥2,070	¥2,680	275	50	16	590
835-8180	PUP100	¥2,483	¥3,220	340	80	24	860

URL <http://www.orange-book.com/>

LOBTEX Stock 1,809 Items **LOBSTER Vise Pliers**

- Features** • Suitable for holding pipes.
- Most suitable for welding work/rivet work.
- Materials** • Special tool steel
- Origin** • Taiwan




Order Unit: 1 Piece LOBTEX Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Max Opening (mm)	SPQ (piece)	Weight (g)
372-6720	VY225N	¥4,395	¥4,650	235	30	2	590

Contact us: 072-980-1111 <http://www.lobtex.co.jp/>

KYOTO TOOL Stock 2,641 Items **Clamp for Welding**

- Features** • Convenient for fixing square iron material/panels, welding work, temporal fixing during rivet work.
- Materials** • Special tool steel
- Origin** • Taiwan



Order Unit: 1 Piece KYOTO TOOL Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Max Opening (mm)	SPQ (piece)	Weight (g)
453-5855	225R	¥3,629	¥3,920	230	41	5	666

URL <http://ktc.jp/>

KYOTO TOOL Stock 2,641 Items **"Panel Clamp"**

- Features** • The lower jaw slides back and forth and clamps panels in the right angle (90°).
- Materials** • Special tool steel
- Origin** • Taiwan



Order Unit: 1 Piece KYOTO TOOL Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Max Opening (mm)	SPQ (piece)	Weight (kg)
373-0263	9AC	¥5,915	¥6,390	230	9.5	1	0.3

URL <http://ktc.jp/>

Toggle Clamps

Hand Vices

Grip Pliers

C-Clamps

L Type Clamp

Clamps for Temporary Structures

Welding Clamps

Hand Clamps

Bar Clamps

Special Clamps

Vices

Parts for Vices