

10K CAST BRONZE, SWING CHECK VALVES

Fig: 065/J10-BNS

Sizes: 3/8-2inch(10-50mm)

SCREWED CAP, SCREWED ENDS.

Standards

. End to End: JIS B2011

. End Connection: JIS B0203

. Wall Thickness: JIS B2011

Test Standard

. JIS B2011

Dimensions

SIZE(inch/mm)	L	L1	H	D1	Kg
3/8 10	55.0	0.0	38.5	0.0	0.00
1/2 15	65.0	0.0	43.0	0.0	0.00
3/4 20	80.0	0.0	51.5	0.0	0.00
1 25	90.0	0.0	58.5	0.0	0.00
1 1/4 32	105.0	0.0	67.0	0.0	0.00
1 1/2 40	120.0	0.0	73.5	0.0	0.00
2 50	140.0	0.0	86.0	0.0	0.00

Material List

NAME OF PART	MATERIAL	SPECIFICATION
BODY	CAST BRONZE	CAC406
CAP	FORGED BRASS	C3771BE
DISC	CAST BRONZE	CAC406

Specifications


10K CAST BRONZE, SWING CHECK VALVES, SCREWED CAP, SCREWED ENDS.

End to End : JIS B2011, End Connection : JIS B0203, Wall Thickness :

JIS B2011, Test Standard : JIS B2011, Sizes :

3/8-2inch(10-50mm), BODY MATERIAL : CAST BRONZE, CAP MATERIAL : FORGED

BRASS, DISC MATERIAL : CAST BRONZE, Fig : 065/J10-BNS



For more details, please refer to the drawing.

Pressure-temperature ratings and other performance data published in this catalog have been developed from our design calculation, in-house testing, field reports provided by our customers and/or published official standards or specifications. They are good only to cover typical applications as a general guideline to users of KITZ products introduced in this catalog. For any specific application, users are kindly requested to contact KITZ Corporation for technical advice, or to carry out their own study and evaluation for proving suitability of these products to such an application. Failure to follow this request could result in property damage and/or personal injury, for which we shall not be liable. Read instruction manual carefully before use.