

# Tubes

## High Temperature Silicone Foam

Used for filling gaps, making circular seals, or fabricated into round parts such as spacers, washers, or stoppers. Silicone is the go to choice for high temperature applications.



Part Number	Shape	Cell Type	Material	Grade	Length	ID	OD	Color	Firmness	Texture	Specs Met
ZUSASSR-T-1	Tube	Closed Cell	Silicone	Standard	5 ft.	1/4"	3/4"	Red	Soft (5 - 8 psi)	Smooth	ASTM D1056 2D2
ZUSASSR-T-2	Tube	Closed Cell	Silicone	Standard	5 ft.	3/8"	7/8"	Red	Soft (5 - 8 psi)	Smooth	ASTM D1056 2D2
ZUSASSR-T-3	Tube	Closed Cell	Silicone	Standard	5 ft.	1/2"	1"	Red	Soft (5 - 8 psi)	Smooth	ASTM D1056 2D2
ZUSASSR-T-4	Tube	Closed Cell	Silicone	Standard	5 ft.	3/4"	1-1/4"	Red	Soft (5 - 8 psi)	Smooth	ASTM D1056 2D2
ZUSASSR-T-5	Tube	Closed Cell	Silicone	Standard	5 ft.	1"	1-1/2"	Red	Soft (5 - 8 psi)	Smooth	ASTM D1056 2D2
ZUSASSR-T-6	Tube	Closed Cell	Silicone	Standard	5 ft.	1/8"	5/8"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-7	Tube	Closed Cell	Silicone	Standard	5 ft.	1-1/4"	1-3/4"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-8	Tube	Closed Cell	Silicone	Standard	5 ft.	1-1/2"	2"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-9	Tube	Closed Cell	Silicone	Standard	10 ft.	1/4"	3/4"	Red	Soft (5 - 8 psi)	Smooth	ASTM D1056 2D2
ZUSASSR-T-10	Tube	Closed Cell	Silicone	Standard	10 ft.	3/8"	7/8"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-11	Tube	Closed Cell	Silicone	Standard	10 ft.	1/2"	1"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-12	Tube	Closed Cell	Silicone	Standard	10 ft.	3/4"	1-1/4"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-13	Tube	Closed Cell	Silicone	Standard	10 ft.	1"	1-1/2"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-14	Tube	Closed Cell	Silicone	Standard	10 ft.	1/8"	5/8"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-15	Tube	Closed Cell	Silicone	Standard	10 ft.	1-1/4"	1-3/4"	Red	Soft (5 - 8 psi)	Smooth	ASTM D1056 2D2
ZUSASSR-T-16	Tube	Closed Cell	Silicone	Standard	10 ft.	1-1/2"	2"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-17	Tube	Closed Cell	Silicone	Standard	2 ft.	1/4"	3/4"	Red	Soft (5 - 8 psi)	Smooth	ASTM D1056 2D2
ZUSASSR-T-18	Tube	Closed Cell	Silicone	Standard	2 ft.	3/8"	7/8"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-19	Tube	Closed Cell	Silicone	Standard	2 ft.	1/2"	1"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-20	Tube	Closed Cell	Silicone	Standard	2 ft.	3/4"	1-1/4"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-21	Tube	Closed Cell	Silicone	Standard	2 ft.	1"	1-1/2"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-22	Tube	Closed Cell	Silicone	Standard	2 ft.	1/8"	5/8"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-23	Tube	Closed Cell	Silicone	Standard	2 ft.	1-1/4"	1-3/4"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2
ZUSASSR-T-24	Tube	Closed Cell	Silicone	Standard	2 ft.	1-1/2"	2"	Red	Soft (5 - 8 psi)	Smooth	ATSM D1056 2D2