

## (E

## **How to Order**







- ∗ SYJ7□2R is only for manifold use.
- 24, 12 VDC/ 100, 110, 200, 220 VAC 24, 12, 6, 5, 3 VDC/100, 110, 200, 220 VAC 24, 12, 6, 5, 3 VDC L plug connector M plug connector M8 connector Grommet DIN terminal G: Lead wire L: With lead wire M: With lead wire MN: Without lead D: With connector Y: With connector WO: Without length 300 mm (Length 300 mm) (Length 300 mm) wire LN: Without MO: Without DO: Without YO: Without W□: With connector H: Lead wire length 600 mm lead wire connector connector connecto LO: Without connector OF- DC compliant AC
- Note) When placing an order for body ported solenoid valve as a single unit, mounting screws for manifold and gasket are not attached. Order them separately, if necessary. (For details, refer to page 1199.)
  - \* LN, MN type: with 2 sockets.
  - Refer to page 1213 for the lead wire length of L and M plug connectors.
    Refer to page 1216 for the connector assembly with cover for L and M plug connectors.
- DIN terminal type "Y" which conforms to EN-175301-803C (former DIN4365C) is also available. For details, refer to page
- \* For connector cable of M8 connector, refer to page 1217.
- \* A M8 connector conforming to IEC60947-5-2 is also available. Refer to page 1210 for details.

Note 1) Enter the cable length symbols in □. Please be sure to fill in the blank referring to page 1217.

